

Manufacturer Declaration

Endress+Hauser Wetzler GmbH+Co. KG, Obere Wank 1, 87484 Nesselwang

declares as manufacturer, that the resistance deviation of the following types of inserts

iTHERM	QuickSens	(ϕ 6 mm Class AA)
iTHERM	QuickSens	(ϕ 3 mm Class AA)
iTHERM	StrongSens	(ϕ 6 mm Class AA)

has been successfully tested to comply with accuracy class AA according to DIN EN 60751:2009-05 in the long-term test described below.

The long-term test performed in the in-house testing laboratory is a cycle test comprising a total of 377 heating cycles.


The time-temperature curve of one heating cycle is described as follows:


Phase	Temperature	Duration
1	40 °C	1 hour
2	65 °C	1 hour
3	40 °C	1 hour
4	135 °C	1 hour

and is finished after 5.3 hours.

This declaration of conformity is only valid for the customer and devices listed in the cover letter of the responsible sales centre which refers to this document. This declaration of conformity is only valid for products being in the delivery status and produced after the following date of issue.

Nesselwang, 04.12.2013
 Endress+Hauser Wetzler GmbH+Co.KG


 ppa Martin Adolf (Director Marketing)


 i.V. Dieter Waldhauser (Head of Div. R&D)